



**FOR MORE INFORMATION  
CALL (818) 991-9997**

**<http://www.biosolutions.org>**

# RLA24 Riser-to-Lid Adapter

Submittal  
Data Sheet




Oreco Systems®  
Incorporated

1-800-348-9843

## Applications

The RLA24 Riser-to-Lid Adapter provides a secure, watertight method of attaching a fiberglass lid to access risers.



## General

The RLA24 Riser-to-Lid Adapter can be attached to the top of a 24" diameter riser (either Ultra-Rib or Perma-Loc) to facilitate bolting the lid to the riser. The adapter has a built-in gasket and 12 pre-drilled and tapped 5/16" holes, ready to accept the stainless steel bolts provided with the lid. The non-gasketed FL24-4B lid can be used, and can be secured using 2 or 4 bolts (4 bolts recommended), in any number of positions for ease-of-use. An adhesive, either MA320 or ADH100, should be used to bond the adapter to the riser.

## Standard Models

RLA24

## Nomenclature

**RLA**    
Indicates adapter diameter (inches)  
24 = 24"  
Riser-to-lid adapter

## Specifications

### Materials of Construction:

RLA24 Riser-to-Lid Adapter: Injection molded ABS  
O-Ring Gasket: EPDM Rubber